

Part Number: [0734156180](#)
Status: Active
Overview: SMPM and SMP RF Connectors
Description: 50 Ohms, SMP Surface Mount Plug, Limited Detent, One Piece Per Bag

Documents:

3D 모델
도면 (PDF) [RoHS 증명서\(PDF\)](#)

일반적 특성	
전체보기	<u>SMPM and SMP RF Connectors</u>
제품명	SMP
스타일	PCB
타입	Subminiature
UPC	800756689494
와이어/케이블 타입	N/A
물리적 특성	
암수구분	플러그
Keying to Mating Part	없음
Net Weight	0.279/g
방향성	일자형
PCB 마운팅	표면실장
포장타입	백 (Bag)
패널마운트	No
패널마운트 방법	N/A
전기적 특성	
Frequency	40 GHz
임피던스	50Ω
납땜 프로세스 정보	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260
원재료 정보	
참고 - 도면번호	
도면	SD-73415-618-001, SD-85305-0232-001



EU ELV
Not Relevant

EU RoHS China RoHS

Compliant with
Exemption 6(c)

REACH SVHC
Contained Per -
ED/61/2018 (27 June
2018)

납
Halogen-Free
Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for
any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
Prop65	Duty-To-Declare
PropRisk	Cancer
PropRisk	Developmental toxicity
PropRisk	Reproductive toxicity
PropSub	Lead and its compounds
RoHS Phthalates	Not Contained

Search Parts in this Series
[73300 Series](#)