

## Han 10B HTE M25 PFT SL



Part number	19 30 010 1131
Specification	Han 10B HTE M25 PFT SL
HARTING eCatalogue	<a href="https://b2b.harting.com/19300101131">https://b2b.harting.com/19300101131</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Panel feed through housing
Type	High construction

### Version

Locking type	Single locking lever
Han-Easy Lock <sup>®</sup>	Yes
Size	10 B
Version	Top entry
Cable entry	1x M25
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0

### Commercial data

Packaging size	1
----------------	---



Pushing Performance

## Commercial data

Net weight	313.9 g
Country of origin	China
Customs tariff number	8538900000

---