

## Han 16B HTE M40 PFT DL



|                    |   |
|--------------------|---|
| Part number        | 19 30 016 1122  |
| Specification      | Han 16B HTE M40 PFT DL  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19300161122">https://b2b.harting.com/19300161122</a> |

### Identification

|                          |                            |
|--------------------------|----------------------------|
| Category                 | Hoods/Housings             |
| Series of hoods/housings | Han <sup>®</sup> B         |
| Type of hood/housing     | Panel feed through housing |
| Type                     | High construction          |

### Version

|                            |   |
|----------------------------|---|
| Locking type               | Double locking lever                              |
| Han-Easy Lock <sup>®</sup> | Yes   |
| Size                       | 16 B  |
| Version                    | Top entry   |
| Cable entry                | 1x M40  |
| Field of application       | Standard hoods/housings for industrial connectors |

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65            |

### Material properties

|  |                                  |
|--|----------------------------------|
| Material (hood/housing)                                    | Aluminium die-cast               |
| Surface (hood/housing)                                     | Powder-coated                    |
| Colour (hood/housing)                                      | RAL 7037 (dust grey)             |
| Material (seal)  | NBR                              |
| Material (locking)   | Polycarbonate<br>Stainless steel |
| Colour (locking)   | RAL 7037 (dust grey)             |
| Material flammability class acc. to UL 94 (locking levers) | V-0                              |

### Commercial data

|                |   |
|----------------|---|
| Packaging size | 1 |
|----------------|---|



Pushing Performance

## Commercial data

|                       |            |
|-----------------------|------------|
| Net weight            | 352.7 g    |
| Country of origin     | China      |
| Customs tariff number | 8538900000 |

---