

ABSL-001 SLIMLINE ROCKER SWITCH

SWITCHES

Specifications

ABSL-001

Rating	6(2)A/250VAC T125/55 1E4 10A/125VAC		
Colour	Black body/01 engraving		
Switch action	Single pole/On-off		
Maximum contact resistance at DC 0.2V 1A	30MΩ		
Minimum insulation resistance	500VDC 100MΩ		
Withstand voltage	AC1500V at 1 min		
Electrical life	More than 10,000 cycles		
Operation force	300~600g		
Operating temperature	-85°C		
Cut out	Z	Y	X
(diagram opposite)	0.75-1.25	19.2	6.8
	1.25-2.0	19.4	6.8
	2.0-3.0	19.6	6.8

Approval VDE, UL

Features

- ROHS compliant
- Housing material:
Nylon #66 UL 94V-2
- Rocker material:
UL 94V-2 #66
- Terminal material:
Copper alloy SN or AG plated
- Contact material:
Ag-Cd-0(12) alloy plated

