

Part Details:-

Part Number	Description
GCM-KIT-C0G-DE-A	CLASS 1 AUTOMOTIVE AEC-Q200 QUALIFIED CAPACITOR KIT

KIT Contents:-

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
1	GCM1555C1HR30WA16	1005M/0402	C0G	50Vdc	0.3pF	±0.05pF	0.55max		20
2	GCM1555C1HR40WA16	1005M/0402	C0G	50Vdc	0.4pF	±0.05pF	0.55max		20
3	GCM1555C1HR50WA16	1005M/0402	C0G	50Vdc	0.5pF	±0.05pF	0.55max		20
4	GCM1555C1HR60WA16	1005M/0402	C0G	50Vdc	0.6pF	±0.05pF	0.55max		20
5	GCM1555C1HR70WA16	1005M/0402	C0G	50Vdc	0.7pF	±0.05pF	0.55max		20
6	GCM1555C1HR80WA16	1005M/0402	C0G	50Vdc	0.8pF	±0.05pF	0.55max		20
7	GCM1555C1HR90WA16	1005M/0402	C0G	50Vdc	0.9pF	±0.05pF	0.55max		20
8	GCM1555C1H1R0BA16	1005M/0402	C0G	50Vdc	1.0pF	±0.1pF	0.55max		20
9	GCM1555C1H2R0BA16	1005M/0402	C0G	50Vdc	2.0pF	±0.1pF	0.55max		20
10	GCM1555C1H3R0BA16	1005M/0402	C0G	50Vdc	3.0pF	±0.1pF	0.55max		20
11	GCM1555C1H4R0BA16	1005M/0402	C0G	50Vdc	4.0pF	±0.1pF	0.55max		20
12	GCM1555C1H5R0BA16	1005M/0402	C0G	50Vdc	5.0pF	±0.1pF	0.55max		20
13	GCM1555C1H6R0BA16	1005M/0402	C0G	50Vdc	6.0pF	±0.1pF	0.55max		20
14	GCM1555C1H7R0BA16	1005M/0402	C0G	50Vdc	7.0pF	±0.1pF	0.55max		20
15	GCM1555C1H8R0BA16	1005M/0402	C0G	50Vdc	8.0pF	±0.1pF	0.55max		20
16	GCM1555C1H9R0BA16	1005M/0402	C0G	50Vdc	9.0pF	±0.1pF	0.55max		20
17	GCM1555C1H100JA16	1005M/0402	C0G	50Vdc	10pF	±5%	0.55max		20
18	GCM1555C1H120JA16	1005M/0402	C0G	50Vdc	12pF	±5%	0.55max		20
19	GCM1555C1H150JA16	1005M/0402	C0G	50Vdc	15pF	±5%	0.55max		20
20	GCM1555C1H180JA16	1005M/0402	C0G	50Vdc	18pF	±5%	0.55max		20
21	GCM1555C1H220JA16	1005M/0402	C0G	50Vdc	22pF	±5%	0.55max		20
22	GCM1555C1H270JA16	1005M/0402	C0G	50Vdc	27pF	±5%	0.55max		20
23	GCM1555C1H330JA16	1005M/0402	C0G	50Vdc	33pF	±5%	0.55max		20
24	GCM1555C1H390JA16	1005M/0402	C0G	50Vdc	39pF	±5%	0.55max		20
25	GCM1555C1H470JA16	1005M/0402	C0G	50Vdc	47pF	±5%	0.55max		20
26	GCM1555C1H560JA16	1005M/0402	C0G	50Vdc	56pF	±5%	0.55max		20
27	GCM1555C1H680JA16	1005M/0402	C0G	50Vdc	68pF	±5%	0.55max		20
28	GCM1555C1H820JA16	1005M/0402	C0G	50Vdc	82pF	±5%	0.55max		20
29	GCM1555C1H101JA16	1005M/0402	C0G	50Vdc	100pF	±5%	0.55max		20
30	GCM1555C1H121JA16	1005M/0402	C0G	50Vdc	120pF	±5%	0.55max		20
31	GCM1555C1H151JA16	1005M/0402	C0G	50Vdc	150pF	±5%	0.55max		20
32	GCM1555C1H181JA16	1005M/0402	C0G	50Vdc	180pF	±5%	0.55max		20
33	GCM1555C1H221JA16	1005M/0402	C0G	50Vdc	220pF	±5%	0.55max		20

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
34	GCM1555C1H271JA16	1005M/0402	C0G	50Vdc	270pF	±5%	0.55max		20
35	GCM1555C1H331JA16	1005M/0402	C0G	50Vdc	330pF	±5%	0.55max		20
36	GCM1555C1H391JA16	1005M/0402	C0G	50Vdc	390pF	±5%	0.55max		20
37	GCM1555C1H471JA16	1005M/0402	C0G	50Vdc	470pF	±5%	0.55max		20
38	GCM1555C1H561JA16	1005M/0402	C0G	50Vdc	560pF	±5%	0.55max		20
39	GCM1555C1H681JA16	1005M/0402	C0G	50Vdc	680pF	±5%	0.55max		20
40	GCM1555C1H821JA16	1005M/0402	C0G	50Vdc	820pF	±5%	0.55max		20
41	GCM1555C1H102JA16	1005M/0402	C0G	50Vdc	1000pF	±5%	0.55max		20