



## SOLDER POTS



### SOLDER POT SELECTOR GUIDE

When ordering pot components, please order by pot catalog numbers.

Catalog No.	Pot Model No.	Wattage	Inside Dimen.	Inside Depth	Max. Temp. °F	Solder Cap. lbs.	Shipping Wt. lbs.
<b>P1200</b>	<b>12</b>	200	1 9/16" diam.	1 1/2"	750	3/4	4
<b>P12003</b>	<b>12C</b>	200	1 9/16" diam.	1 1/2"	900	3/4	4 1/4
<b>P120020</b>	<b>12T</b>	250	1 9/16" diam.	1 1/2"	650	3/4	6 1/4
<b>P2000</b>	<b>20</b>	250	2" diam.	1 1/2"	1200	1 1/4	7
<b>PD24</b>	<b>PD24</b>	250	2" diam.	1 1/2"	1100	1 1/4	5 1/2
<b>PD33</b>	<b>PD33</b>	350	3" x 3"	1 1/2"	850	4 1/4	8
<b>P3600</b>	<b>36</b>	250	2 1/2" diam.	1 3/4"	750	2 1/4	4
<b>P36003</b>	<b>36C</b>	250	2 1/2" diam.	1 3/4"	900	2 1/4	4 1/4
<b>P360020</b>	<b>36T</b>	250	2 1/2" diam.	1 3/4"	625	2 1/4	6 1/4
<b>P3700</b>	<b>37</b>	650	3 1/2" diam.	1 3/4"	800	5	7
<b>P37003</b>	<b>37C</b>	650	3 1/2" diam.	1 3/4"	1000	5	7 1/2
<b>P370020</b>	<b>37T</b>	650	3 1/2" diam.	1 3/4"	650	5	9 1/8
<b>P7000</b>	<b>70</b>	650	4 3/4" diam.	1 3/4"	750	9	6 3/4
<b>P700020</b>	<b>70T</b>	650	4 3/4" diam.	1 3/4"	650	9	8
<b>P710020</b>	<b>71T</b>	1000	3 1/8" diam.	4 1/4"	900	9 1/2	14
<b>PD74</b>	<b>PD74</b>	1000	3 1/8" diam.	4 1/4"	900	9 1/2	13 1/2
<b>P7500</b>	<b>75</b>	650	4 3/4" x 4 3/4"	1 3/4"	750	11 3/4	8
<b>P750020</b>	<b>75T</b>	650	4 3/4" x 4 3/4"	1 3/4"	650	11 3/4	9 1/8
<b>P800020</b>	<b>80T</b>	1200	6" x 12"	1 7/8"	650	33	28

Models with suffix "C": Features a thermocape, a device which adds approximately 150°F to the temperature of standard models without the necessity of increasing the wattage of the heating element.

Models with suffix "T": Features an adjustable thermostat for selecting the optimum operating temperature.

**ESICO·TRITON**

P. O. Box 247 2 Esico Lane Deep River, Connecticut 06417-0247

I N T E R N A T I O N A L

Phone: 800.526.8661 Fax: 860.526.9524 E-mail: sales@esicotriton.com