



1/2" x 30m/100' Hi-Viz® Orange Fiberglass SAE/Metric Dual Sided Tape Measure

Catalog Number: FM030CME



– Overview

13mm (1/2") x 30m (100') Hi-Viz® Orange Fiberglass, 2-Sided,
Metric/English

– Features

1/2" x 30m/100' Hi-Viz® Orange Fiberglass SAE/Metric Dual Sided Tape
Measure

- Open four arm frame design protects blade without trapping dirt in the case
- Lightweight case for easy handling and transport
- Dual material grip is elevated above the reel to prevent contact between the reel and your knuckles
- Versatile folding end hook for use in multiple applications
- Rewind reel tucks away for protection during storage
- Dual sided blade measures feet, inches and 1/8ths, on one side, and meters, centimeters, and millimeters on the other, with red instantaneous foot and meter numbers
- Blade style: C4

- Specifications

UPC	037103224156
Set	No
Blade Length	30 m,100 ft
Packaging	Carded
Blade Width	13 mm,1/2 in
Case Color	Orange
Blade Style	C4
Blade Finish	Fiberglass
Replacement Blade Cat No.	None
Weight (Catalog)	1.47 kg