



48-32-4062

## SHOCKWAVE™ Impact Duty Driver Bit Set - 74PC

★★★★★ (0) Write a review

Our SHOCKWAVE™ Impact Duty driver bits are engineered to be the most durable, best fitting impact driver bits on the market. We created optimized Shock Zone™ bit geometry that is unique for each bit tip type. This provides up to 30X longer life and absorbs 3X more torque versus other impact bits. SHOCKWAVE™ driver bits deliver extreme durability for the most demanding applications. Precise Fit Custom Machined Tips™ prevent bit stripping and reducing wobble while in use. Our custom Alloy76™ steel maximizes bit resistance to wear and shock. Our SHOCKWAVE™ Impact Duty driver bits can be used in both impact drivers or drill drivers. The 74 piece set comes with a wide assortment of driver bits so you can get the job done right every time.

Close

### INCLUDES:

- (1) SHOCKWAVE™ Compact Magnetic Bit Holder
- (1) 1/4" Magnetic Nut Driver

- (1) 5/16" Magnetic Nut Driver
- (1) 3/8" Socket Adapter
- (2) Phillips Bit 1" P1
- (11) Phillips Bit 1" P2
- (1) Philips Bit 1" PR2
- (3) Phillips Bit 1" P3
- (2) Square Bit 1" SQ1
- (4) Square Bit 1" SQ2
- (2) Square Bit 2" SQ3
- (1) Slotted 1" #8 Bit
- (2) Slotted 1" #10 Bit
- (1) INSERT BIT HEX 1/4"
- (1) INSERT BIT HEX 1/8"
- (1) INSERT BIT HEX 3/16"
- (1) INSERT BIT HEX 9/64"
- (1) INSERT BIT HEX 5/32"
- (1) Hex3mm 312 Power Groove Bit
- (1) Hex4mm 312 Power Groove Bit
- (1) Hex5mm 312 Power Groove Bit
- (1) Hex6mm 312 Power Groove Bit
- (1) TORX® Bit 1" T10
- (2) TORX® Bit 1" T15
- (4) TORX® Bit 1" T20
- (7) TORX® Bit 1" T25
- (2) TORX® Bit 1" T27
- (2) TORX® Bit 1" T30
- (2) P2 2" Power Groove Bit
- (1) P3 2" Power Groove Bit
- (2) SQ2 2" Power Groove Bit
- (1) SQ3 2" Power Groove Bit
- (1) T20 2" Power Groove Bit
- (1) T25 2" Power Groove Bit
- (1) P2 3 1/2" Power Groove Bit
- (1) SQ2 3 1/2" Power Groove Bit
- (1) T25 3 1/2" Power Groove Bit
- (1) T20/T25 Double Ended Bit

(1) P2/SL #10 Double Ended Bit

(1) P2/SQ2 Double Ended Bit

(1) P2/T25 Double Ended Bit

**Close**

Where To Buy

**KEY FEATURES**

**SPECIFICATIONS**

**REVIEWS**

Optimized Shock Zone™ geometry absorbs peak torque and prevents breaking

Precise Fit Custom Machined Tip™ prevents stripping and reduces wobble

Custom Alloy76™ Steel maximizes resistance to wear and shock

Up to 30x Life

Absorbs 3X more torque vs. impact bits

1/4"-20 Threaded Mount

Includes 74-pieces

**PRODUCT SPECIFICATIONS**

---

Size 74PC

---

**REVIEWS**



Be the first to review this product