

TECHNICAL SPECIFICATION

	Infrared	K-Type	Humidity	Wet Bulb/Dew Point
Range	-50° to +550°C	-50° to 1370°C	0% to 100%RH	-20° to 60°C
Resolution	0.1°C	0.1°C(<1000) 1°C(>1000)	0.1%RH	0.1°C
Accuracy	±1.5% or ±2°C	±1.5% or ±1.5°C	±3%RH (30 to 70%RH) 5%RH (others)	±1.5°C
Response Time	Less than 500ms			
Distance to Spot Size Ratio	13 to 1 at focal point			
Emissivity	0.1 to 1 -0 adjustable			
Power	1 x 9V PP3 alkaline battery (LR-61)			
Dimensions	115 x 46 x 160			
Weight	240g			