

H1-9040P



- Compatible for use with bolt (flange) fitted compression drivers
- Hard-wearing reinforced polymer

General Specifications

Horn type	Exponential
Radiation pattern	90° x 40°
Horn material	ABS
Baffle cut-out	165mm/6.5in x 260mm/10.2in
Driver mounting detail	Flange: 2xM6 holes on 76mm/3in PCD
Throat exit	25.1mm/1in
Height	199mm/7.8in
Width	318mm/12.5in
Depth	208mm/8.2in
Weight	0.66kg/1.45lb

Packed Dimensions & Weight

Single pack size W x D x H	350mm x 220mm x 230mm /13.7in x 4.7in x 4.7in
Single pack weight	1.0kg/3.3lb
Multi pack size W x D x H	650mm x 500mm x 240mm /25.6in x 20in x 9.4in
Multi pack weight	10kg/22lb