



PRODUCT #: 880430

LEDLENSER EXH8

Those who want to maintain an overview and need their hands free in hazardous areas should keep the Ledlenser EXH8 in mind. Or better yet, have it right on their heads: this headlamp offers maximum safety from explosions in almost any situation with gas or dust hazards – and it's absolutely comfortable to wear. It is the first headlamp for Ex Zone 0/20 with the patented Advanced Focus System. So this headlamp is a customized light for every use.

KEY FEATURES:




- Magnetic Switch for easy operation with gloves and protective equipment
- Patented Advanced Focus System
- Long battery life (up to 40 hours)
- Dustproof and protected against powerful water jets (IP66)
- Red rear light as a position marker

APPROVALS:

- Class 1, Division 1, Groups A,B,C,D;
- Class II, Division 1, Groups E,F,G; Class III, Temperature Code: T4
- ATEX: II 2G Ex ib IIC T4 Gb, II 2D Ex ib op is IIIC T135°C Db



WEIGHT: 12.17 oz. | 345 g
BATTERY: 3x alkaline AA

FL1 STANDARD	MAX	MIN
	180 LUMENS	50 LUMENS
	120m	65m
	15h	40h



Industry-leading Warranty

All Ledlenser products come backed by our industry-leading seven-year warranty. For more information about our warranty, please visit ledlenserusa.com.

ADDRESS:

Ledlenser USA
PO Box 20446
Portland, OR 97294

PHONE:

Local: (503) 408-5301
Toll Free: (800) 650-1245

WEB:

www.ledlenserusa.com