pro-**Power**

RoHS Compliant

Benefits:

- Pre-cut for rapid removal from backing sheet
- Print using ordinary standard office laser printer and the pro-Power software
- · Choice of 3 sizes; ideal for faceplates, outlets and equipment
- · For colour font / background use colour laser printer

Description:

Labels made from highly durable 50 micron polyester ensuring maximum opacity Also incorporating a strong acrylic adhesive for long-term bonding. For best results use on a clean, dry, grease-free, smooth surface. Special laser printable surface ensures high quality and consistency of print.

Available in three sizes; 22mm × 7mm, 50mm × 10mm and 60mm × 25mm. Ideal for faceplates, outlets or for general internal applications.

The free pro-Power software is downloadable from: <u>http://www.silverfox.co.uk/product/farnell-pro-power-software/</u>

Recommended printing via straight printer path.

Technical Data

Material	50 micron self-adhesive polyester
Printer Type	Laser printers only

Product Testing

Test	Method		
Moisture Resistance	MIL-STD-202G Method 106G		
Low Temperature 72 hours @ -40°C	MIL-STD-810F Method 502.4		
High Temperature 2000 hours @ 70°C to 100°C*	MIL-STD-202G Method 108A		
Hydrogen Sulphide	H ₂ S Sour Gas Exposure (2% H ₂ S)		
UV Weathering 3,000 hours	ISO 4982 Part 3 Method A Cycle 1		
Salt Mist Spray	IEC60068-2-52 Test Kb Salt Mist (Cyclic)		

Note:

* Samples were subjected to 500 hours @ 70°C, followed by 500 hours @ 85°C followed by 1,000 hours @ 100°C.

This label is designed for internal use. For external use the user must determine the suitability of this label for their particular application.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk



Specification Table

Label Dimensions (mm)	Printable (mm)	Sheet Size	Labels per Sheet	Sheets per Pack	Colour	Part Number
22 × 07	21 × 6		280			2075102
50 × 10	49 × 9	A4	75	10	White	2075103
60 × 25	59 × 24		30			2075104

Part Number Table

Description	Part Number
Label, Wht, 22mm × 7mm, 280/Sheet, PK10	2075102
Label, Wht, 50mm × 10mm, 75/Sheet, PK10	2075103
Label, Wht, 60mm × 25mm, 30/Sheet, PK10	2075104

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage raising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk

