

C.A 755 - C.A 757

Digital testers



Testers which think they're multimeters!

- Automatic recognition of AC and DC
- Automatic recognition of resistors, diodes and capacitors
- Automatic calibre selection
- Hazardous voltage indication
- Removable test probes

600 V CAT III

IEC 61010-2-033



Measure up



C.A 755 - C.A 757

Ergonomics

The C.A 755 and C.A 757 have a large backlit digital display with a **3,000-count resolution** allowing users to view their measurement results as well as all the function symbols, calibres and battery-level indications.

The removable test probes mean they can be replaced at lower cost and offer users the possibility of choosing different probes for different uses, if required.



There is a built-in system for stowing these test probes in the casing, which offers IP54 ingress protection. The shapes of the test probes and casing are designed for comfortable handling.



Removable test probes

Rotary switch for selecting the measurement

Large backlit LCD screen

IP54 casing
Withstands falls from a height of up to 2 m

Accessories which simplify your everyday work

► Measurement adapter for 2P+E sockets

Ideal for use with these multimeters, the **C.A 753** allows measurements in total safety on European and Schuko 2P+E sockets. Its design guarantees mechanical and electrical contact with all types of test probes (Ø 2 mm, Ø 4 mm, IP2x, etc.). It also indicates when a voltage > 200 V is present, as well as showing the phase position..



► The **bag**, compatible with the Multifix accessory proposed as an option, can be used to transport and stow the instrument, its accessories and replacement parts so that everything is available for use at any time.



► **The removable test probes** can be changed to suit the application and the measurement conditions.



P01102152Z



P01102153Z



P01102154Z

Slimline and flexible, the **MiniFlex®** measuring accessory supplied with the **C.A 757** can be used to measure currents up to 300 A, including on conductors which are difficult to access.



▼ Safe and easy to use

The **C.A 755 and C.A 757 multitesters** meet the specific needs of professionals working on Low-Voltage electrical installations. Their numerous automated functions help to prevent the usual handling errors. With their **600 V CAT III** safety and their compliance with the IEC 61010-2-033 standard, they are intended for electricians, heating engineers, mechanics, maintenance technicians, etc.

They offer **exceptional safety** for testers:

- ▶ double insulation
- ▶ protection up to 6 kV for voltage measurements (electric shocks)
- ▶ protection up to 1,000 V for continuity testing and resistance or capacitance measurements
- ▶ protection against dust with their IP54 casing

No-contact voltage detection and hazardous voltage indication are both available.



▼ Applications

In addition to testing the electrical power supply or switching systems, checking wired connections, monitoring consumption (current) and verifying the operation of an electrical appliance or installation, these new Chauvin Arnoux® testers can also be used to troubleshoot failures or faults and test electronic components.



The C.A 755 & C.A 757 are effective in all circumstances:

- **Troubleshooting on distribution switchboards** with the possibility of identifying the phase and neutral **without tripping the RCDs.**
- **DC and AC voltage measurements** to check the different voltages present on the terminals.
- **Audible continuity test**
- **DC voltage measurements** for preventive maintenance on backup batteries.
- **Resistance measurement:** identification of the motor windings and checking of the resistors.
- **Current measurement** on residential switchboards and junction boxes: the C.A 757's MiniFlex flexible sensors mean current measurements are always easy.
- **Diode tests** for maintenance of DC power supply systems and checking of bridge rectifiers.

C.A 755 - C.A 757

Voltage and continuity testers

TECHNICAL SPECIFICATIONS		C.A 755	C.A 757
DC voltage	Measurement range	3 mV to 1,000 V – 4 calibres	
	Resolution	1 mV to 1 V	
AC voltage	Measurement range	100 mV to 1,000 V – 4 calibres	
	Resolution	1 mV to 1 V	
Impedance		10 M Ω	
No-contact voltage detection		Quick detection of any 230 V 50/60 Hz conductor at a distance of approx. 5 cm	
Resistance	Measurement range	0.3 Ω to 30 M Ω – 6 calibres	
	Resolution	0.1 Ω to 0.01 M Ω	
Continuity		audible continuity indication for R \leq 30 Ω	
Capacitance	Measurement range	400 pF to 30 mF	
	Resolution	0.001 nF to 0.01 mF	
Diodes		for junction voltages between 300 mV and 2 V	
Current via current sensor	Measurement range	-	500 mA to 300 A (2 calibres)
	Resolution	-	0.01 A to 0.1 A
Electrical safety		600 V CAT III, IEC 61010-1, IEC 61010-031, IEC 61010-032, IEC 61010-033	

GENERAL SPECIFICATIONS

Power supply	2 x 1.5 V batteries (LR03 or AAA)
Battery life	100 hours with alkaline batteries – Automatic standby after 10 minutes
Dimensions / weight	180 x 52 x 45 mm / Weight approx. 200 g

References to order

TO ORDER

C.A 755 P01191755

Delivered with 1 set of extra-fine test probes CAT III/CAT IV (red/black), 2 x 1.5 V AAA / LR3 alkaline batteries, 1 user manual in 5 languages, 1 safety datasheet, 1 verification certificate.

C.A 757 P01191757

Same as the C.A 755 plus 1 MiniFlex[®] sensor with a loop length of 250 mm, a connection cable 1 m long and a specific connector for C.A 757, 1 Velcro strap.



ACCESSORIES & REPLACEMENT PARTS

1 set of black/red CAT III/IV test probes	P01102152Z
1 set of black/red \varnothing 2 mm test probes, CAT II	P01102153Z
1 set of black/red \varnothing 4 mm test probes, CAT II	P01102154Z
MA101-250 current sensor for C.A 757	P01120591
C.A 753	P01191748Z
Velcro strap x 5	P01102113
1.5 V LR3/AAA alkaline battery (x 1)	P01296032
Bag compatible with MultiFix accessory, 120 x 200 x 60	P01298074
MultiFix mounting accessory	P01102100Z

MultiFix mounting accessory ▶



◀ Bag compatible with MultiFix accessory

CHAUVIN ARNOUX
GROUP

FRANCE
Chauvin Arnoux
190, rue Championnet
75876 PARIS Cedex 18
Tel: +33 1 44 85 44 38
Fax: +33 1 46 27 95 59
export@chauvin-arnoux.fr
www.chauvin-arnoux.com

UNITED KINGDOM
Chauvin Arnoux LTD
Unit 1 Nelson Ct, Flagship Sq, Shaw Cross Business Pk
Dewsbury, West Yorkshire - WF12 7TH
Tel: +44 1924 460 494
Fax: +44 1924 455 328
info@chauvin-arnoux.co.uk
www.chauvin-arnoux.com

MIDDLE EAST
Chauvin Arnoux Middle East
P.O. BOX 60-154
1241 2020 JAL EL DIB - LEBANON
Tel: +961 1 890 425
Fax: +961 1 890 424
camie@chauvin-arnoux.com
www.chauvin-arnoux.com

For assistance and ordering