

# PRODUCT DATASHEET

## FLOODLIGHT 20 W 6500 K IP65 BK

FLOODLIGHT 20 | Luminaire with symmetrical light output with 20 W



### AREAS OF APPLICATION

- Replacement for floodlights with halogen lamps
- Car parks and underpasses
- Public areas
- Building facades
- Construction areas
- D-sign according to EN 60598-2-24 for fire-risk commercial unit, f. e. by accumulation of dust

### PRODUCT BENEFITS

- Energy savings of up to 90 % compared to halogen lamp floodlights
- Frosted cover made of tempered glass for uniform illumination
- Optimized weight and size due to compact design
- 3 years guarantee

### PRODUCT FEATURES

- Luminaire efficacy: up to 110 lm/W
- Symmetrical beam angle: 100° x 100°
- Mounting bracket for up to 180° tilting
- Type of protection: IP65
- Impact resistance: IK07
- Ambient temperature in operation: -20...+50 °C
- Connection via 1 m cable, wiring required



**TECHNICAL DATA**

Electrical data

Nominal wattage	20.00 W
Operating mode	Integrated LED driver
Nominal voltage	220...240 V
Power factor $\lambda$	> 0.90
Mains frequency	50/60 Hz


Photometrical data

Color temperature	6500 K
Luminous flux	2200 lm
Luminous efficacy	110 lm/W
Standard deviation of color matching	$\leq 5$ sdc <sub>m</sub>
Light color (designation)	Cool Daylight
Color rendering index Ra	$\geq 80$

Light technical data

Beam angle	100 ° x 100 °
------------	---------------

Dimensions & weight



Length	130.0 mm
Width	140.0 mm
Height	41.0 mm
Product weight	560.00 g
Cable length	1000 mm

Colors & materials

Body material	Polycarbonate (PC)
Housing color	Black

<b>Product color</b>	Black
<b>Cover material</b>	TEMPERED GLASS

### Temperatures & operating conditions

<b>Ambient temperature range</b>	-20...50 °C
----------------------------------	-------------

### Lifespan

<b>Lifespan L70 at 25 °C</b>	50000 h
<b>Lifespan L80 at 25 °C</b>	30000 h
<b>Lifespan L90 at 25 °C</b>	15000 h

### Additional product data

<b>Mounting type</b>	Surface
<b>Mounting location</b>	Wall / Floor



### Capabilities

<b>Dimmable</b>	No
<b>Type of connection</b>	Cable, 3-pole
<b>LED module replaceable</b>	Not replaceable

### Certificates & standards

<b>Protection class IK (shock resistance)</b>	IK07
<b>Photobiological safety group</b>	RG 0
<b>Protection class</b>	I
<b>Type of protection</b>	IP65
<b>Standards</b>	CE/CB/TÜV SÜD/EAC/RoHS

Light Distribution



LDC typ cone

LDC typ polar

LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075097520	FLOODLIGHT 20 W 6500 K IP65 BK	Shipping carton box 10	301 mm x 247 mm x 221 mm	16.43 dm <sup>3</sup>	6730.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see

- ▶ [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.