

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190700069

Status:

Active

Overview:

Solderless Terminals

Description:

InsulKrimp Ring Tongue Terminal for 14-16 AWG Wire



|                                                              |                                                              |
|--------------------------------------------------------------|--------------------------------------------------------------|
| Documents:                                                   |                                                              |
| <a href="#">3D Model</a>                                     | <a href="#">Product Specification PS-19902-011-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Product Specification PS-19902-013-001 (PDF)</a> |
| <a href="#">Product Specification PS-19902-009-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |

|                             |                                                      |
|-----------------------------|------------------------------------------------------|
| Agency Certification        |                                                      |
| CSA                         | LR18689                                              |
| UL                          | E32244                                               |
| General                     |                                                      |
| Product Family              | Ring and Spade Terminals                             |
| Series                      | 19070                                                |
| Crimp Quality Equipment     | Yes                                                  |
| Mil-Spec                    | N/A                                                  |
| Overview                    | Solderless Terminals                                 |
| Product Name                | InsulKrimp                                           |
| Type                        | Ring                                                 |
| UPC                         | 800753069220                                         |
| Physical                    |                                                      |
| Barrel Type                 | Closed                                               |
| Color - Resin               | Natural                                              |
| Flammability                | 94V-0                                                |
| Insulation                  | PVC                                                  |
| Material - Plating Mating   | Tin                                                  |
| Net Weight                  | 0.500/g                                              |
| Packaging Type              | Bag                                                  |
| Stud Size                   | 5-6 (M3-3.5)                                         |
| Wire Insulation Diameter    | 4.40mm max.                                          |
| Wire Size AWG               | 14, 16                                               |
| Wire Size mm²               | 1.30-2.00                                            |
| Solder Process Data         |                                                      |
| Lead-freeProcess Capability | N/A                                                  |
| Material Info               |                                                      |
| Engineering Number          | BB-223-06X                                           |
| Reference - Drawing Numbers |                                                      |
| Product Specification       | PS-19902-009-001, PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing               | SD-19070-008                                         |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per                                             |               |
| -ED/01/2018 (15                                               |               |
| January 2018)                                                 |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

19070 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION