

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191600009](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 12-22 AWG Wire

Documents:

Drawing (PDF)	Packaging Specification PK-19408-109-001 (PDF)
Product Specification PS-19902-013-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	19160
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	Closed-End Insulated
UPC	800753110182

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.689/g
Packaging Type	Carton
Temperature Range - Operating	105°C
Wire Insulation Diameter	6.86mm max.
Wire Size AWG	12, 14, 16, 18, 20, 22

Electrical

Voltage - Maximum	600V
-------------------	------

Material Info

Engineering Number	NC-2212
--------------------	---------

Reference - Drawing Numbers

Packaging Specification	PK-19408-109-001
Product Specification	PS-19902-013-001
Sales Drawing	SD-19160-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Prop65

RoHS Phthalates

Green Image

Not Relevant

Compliant

Not Contained

Search Parts in this Series

[19160 Series](#)