

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640074](#)
Status: **Active**
Overview: [Splices](#)
Description: Perma-Seal 3-Way Connector Assembly for 10-12 AWG Wire

Documents:

Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19902-011-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Splices
Series	19164
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	3 Way, Perma-Seal
UPC	800753113589

Physical

Barrel Type	Closed
Color - Resin	Yellow
Insulation	NiAc
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	6.344/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	7.87mm max.
Wire Size AWG	10, 12

Electrical

Voltage - Maximum	600V
-------------------	------

Material Info

Engineering Number	SC-2YCX
--------------------	---------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19164-051, SD-19204-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Missing Compliance Data
RoHS Phthalates	Not Contained

Search Parts in this Series

[19164](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION