

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192750005**
Status: **Active**
Overview: Quixon Terminals
Description: Quixon Quick Disconnect, Avikrimp Style, Female, Partially Insulated Blue, 14-16 AWG, Loose

Documents:

Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19902-011-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E79133

General

Product Family	Quick Disconnects
Series	<u>19275</u>
Comments	Low Insertion Force
Crimp Quality Equipment	Yes
Insulated	Partial
Overview	<u>Quixon Terminals</u>
Product Name	Avikrimp, Quixon
Type	Quick Disconnect
UPC	884982565050

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.958/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	0.41mm
Tab Width	7.87mm
Temperature Range - Operating	-55°C to +105°C
Wire Insulation Diameter	3.51mm
Wire Size AWG	14, 16

Electrical

Voltage - Maximum	300V
-------------------	------

Material Info

Engineering Number	BB-8141-LIF
--------------------	-------------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19275-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

19275 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION