

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0194200010
Status: Active
Overview: MX150L Industrial Sealed Connector System
Description: MX150L Female Terminal for 18-22 AWG Wire, Tin Plated

Documents:

[Drawing \(PDF\)](#)
[Product Specification PS-19417-001-001 \(PDF\)](#)
[Packaging Specification PK-19420-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)
[Product Literature \(PDF\)](#)

Agency Certification

CSA LR18689
UL E152602

General

Product Family Crimp Terminals
Series 19417
Application Power, Wire-to-Board, Wire-to-Wire
Comments UL E152602
Crimp Quality Equipment Yes
Overview MX150L Industrial Sealed Connector System
Packaging Alternative 19420-0002 (Reel)
Product Literature Order No 987650-2181
Product Name MX150L
UPC 822348035786

Physical

Flammability 94V-0
Gender Female
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.352/g
Packaging Type Bag
Plating min - Mating 1.905µm
Plating min - Termination 1.905µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.36-2.74mm
Wire Size AWG 18, 19, 20, 22
Wire Size mm² N/A

Material Info

Reference - Drawing Numbers

Packaging Specification PK-19420-001
Product Specification PS-19417-001-001
Sales Drawing SD-19420-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19417 Series

Mates With

19417

Use With

19418