


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0430300005](#)
Status: **Active**
Overview: Micro-Fit 3.0 Connector System Product Family
Description: Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Reel

Documents:

3D Model	Product Specification TS-43045-002-001 (PDF)
Drawing (PDF)	Packaging Specification PK-43030-001 (PDF)
Product Specification PS-43045 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-43045-001 (PDF)	Product Literature (PDF)



General

Product Family	Crimp Terminals
Series	43030
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Micro-Fit 3.0 Connector System Product Family
Packaging Alternative	43030-0011 (Loose)
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0
UPC	800754369206

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.057/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.27mm max.
Wire Size AWG	26, 28, 30
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	8.5A
-------------------------------	------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43030-001
Product Specification	PS-43045, PS-43045-001, TS-43045-002-001
Sales Drawing	SD-43030-****

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[43030 Series](#)

Use With

[43025](#) , [43645](#) Micro-Fit 3.0 Receptacle Housings, [44133](#) Micro-Fit BMI Panel Mount Receptacle Housings