

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **051353200**
Status: **Active**
Overview: MicroClasp Wire-to-Board System
Description: 2.00mm Pitch MicroClasp Wire-to-Board Receptacle Housing, Positive Lock, Dual Row, 32 Circuits, White

Documents:

[3D Model](#) [Packaging Specification SPK-51353-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-51353-003-001 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series [51353](#)
Application Signal, Wire-to-Board
Overview [MicroClasp Wire-to-Board System](#)
Product Name MicroClasp
UPC 756054235867


Physical

Circuits (maximum) 32
Color - Resin White
Flammability 94V-0
Gender Receptacle
Glow-Wire Capable No
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 1414.000/mg
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.00mm
Stackable No
Temperature Range - Operating -25° to +85°C

Material Info

Reference - Drawing Numbers

Packaging Specification SPK-51353-001-001
Product Specification PS-51353-003-001
Sales Drawing SD-51353-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[51353](#) Series

Mates With

[55917](#) Vertical Header with Kinked PC Tails,
[55959](#) Right Angle Header, [501844](#) Vertical Header

Use With

[56134](#) Terminal