

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0745460405](#)
Status: **Active**
Overview: [iPass Connector System](#)
Description: iPass PCIe x4 Cable Assembly, 26 AWG, 5.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR64395
 UL E72548

General

Product Family Cable Assemblies
 Series [74546](#)
 Assembly Configuration Dual Ended Connectors
 Connector to Connector PCI Express-to-PCI Express
 Overview [iPass Connector System](#)
 Product Name iPass, PCI Express
 UPC 822348864867

Physical

Cable Length 5.0m
 Circuits (Loaded) 38
 Gender Male-Male
 Lock to Mating Part Yes
 Material - Metal Zinc Alloy
 Net Weight 733.895/g
 Packaging Type Bag
 Pitch - Mating Interface 0.80mm
 Single Ended No
 Waterproof / Dustproof Yes
 Wire Insulation Diameter N/A
 Wire Size AWG 26
 Wire/Cable Type Round

Electrical

Current - Maximum per Contact 1.0A
 Shielded Yes
 Voltage - Maximum 30V DC

Material Info

Reference - Drawing Numbers

Sales Drawing SD-74546-400



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
 ED/61/2018 (27 June
 2018)

C,C'-
 azodi(formamide)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[74546 Series](#)

Mates With

[75586 iPass Receptacle](#)

Use With

[74540 PCIe Guide Frame](#)