

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0834219043

Status:

Active

Overview:

Commercial Micro-D High-Density Connectors

Description:

Commercial Micro-D, CMD Single Ended, 9 Circuits, Female - Pigtail, 0.91m Length

Documents:

Drawing (PDF)

Product Specification PS-83421-001-001 (PDF)

Packaging Specification PK-83422-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Assembly Configuration

Connector to Connector

Overmolded

Overview

Product Name

UPC

Cable Assemblies

83421

Single Ended Connector

Commercial Micro-D-to-Pigtail

Yes

Commercial Micro-D High-Density Connectors

Commercial Micro-D

800756424705

Physical

Cable Length

Circuits (Loaded)

Gender

Lock to Mating Part

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Single Ended

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

0.91m

9

Female-Pigtail

None

Gold

Tin

142.110/g

Bag

0.127µm

1.270µm

Yes

Crimp or Compression

.225mm (5.720") max.

28

N/A

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-83422-001

PS-83421-001-001

SD-83421-9023



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

83421 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION