

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0845050003](#)
Status: **Active**
Overview: XRC (Extra Rugged Circular) Sealed Plugs and Receptacles
Description: XRC Sealed Plug with Pin Insert, Shell Size 24, 31 Circuits, with Collar

Documents:

[3D Model](#) [Packaging Specification PK-84501-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84501-001-001 \(PDF\)](#)

Agency Certification

UL E152602

General

Product Family Crimp Housings
 Series [84505](#)
 Application Power, Wire-to-Wire
 Comments IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)

Overview

XRC (Extra Rugged Circular) Sealed Plugs and

Receptacles
 XRC
 883906514983

Physical

Circuits (maximum) 31
 Circuits Detail 31
 Color - Resin Black
 Flammability 94V-0
 Gender Plug
 Glow-Wire Capable No
 Keying to Mating Part Yes
 Lock to Mating Part Yes
 Net Weight 60.730/g
 Number of Rows 0
 Packaging Type Tray
 Panel Mount Yes
 Pitch - Mating Interface N/A
 Pitch - Termination Interface N/A
 Temperature Range - Operating -40° to +130°C

Material Info

Reference - Drawing Numbers

Packaging Specification PK-84501-001-001
 Product Specification PS-84501-001-001
 Sales Drawing SD-84505-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[84505](#) Series

Mates With

[84506](#) Receptacle

Use With

[84524](#) XRC Sealed Terminal Pin