


KEMET Part Number: FM0H104ZF
(USCFM00H104Z00)



FM, Supercapacitors, Radial Molded, Commercial Grade, 0.1 F, -20/+80%, 5.5 VDC, Wire Leads, Lead Spacing = 5mm



Dimensions	
W	10.5mm +/-0.5mm
H	11.5mm +/-0.5mm
T	6.5mm +/-0.5mm
S	5mm +/-0.5mm
LL	5mm +/-1mm
G	0.4mm +/-0.1mm
LT1	0.5mm +/-0.1mm
LT2	0.4mm +/-0.1mm

Packaging Specifications	
Lead:	Wire Leads
Packaging:	Bulk, Bag

General Information	
Supplier:	KEMET
Series:	FM
Description:	Radial Molded Double Layer Capacitor
RoHS:	Yes
Miscellaneous:	DischargeValue = 0.13 F

Specifications	
Capacitance:	0.1 F
Capacitance Tolerance:	-20/+80%
Voltage DC:	5.5 VDC
Temperature Range:	-25/+70C
Rated Temperature:	70C
Resistance:	100000 mOhms (1kHz)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

