



VT-701 GU10 FIXED FIRE RATED DOWNLIGHT FITTING IP20-SATIN NICKEL

Dimensions  
**115x80mm**


SKU:3680

**3 YEARS**  
WARRANTY



## Technical Information

Cutting Size: 65mm	Dimmable: No
Unit Color: SATIN NICKEL	Warranty (Years): 3
Body Type: STEEL	Operation Temperature: -25 to +50°C
IP Rating: IP20	Input Power: AC:220-240V,50/60Hz



## Features

- ✓ Fire rated to resistance of 90 Mins
- ✓ Swift connection - Loop in loop out wiring
- ✓ Effective acoustic installation and air leakage protection
- ✓ Available in Chrome, Satin Nickle & White Color
- ✓ High quality constructed durable steel body
- ✓ IP65 Protected for Outdoor use - IP 20 Protected for Indoor use
- ✓ Spring Clips for safer installation and easy Maintenance

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.2316
Unit CBM	0.000899

### Listing Details

EAN Code	3800157626859
Commodity Code	9405109890

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
---------------------------------	----

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES