



VT-701 GU10 FIXED FIRE RATED DOWNLIGHT FITTING IP20-WHITE

Dimensions
115x80mm

SKU:3681

3 YEARS
WARRANTY



Technical Information

| | | | |
|---------------|-------|------------------------|---------------------|
| Holder Type: | GU10 | IP Rating: | IP20 |
| Shape: | Round | Dimmable: | No |
| Cutting Size: | 65mm | Warranty (Years): | 3 |
| Unit Color: | WHITE | Operation Temperature: | -25 to +50°C |
| Body Type: | STEEL | Input Power: | AC:220-240V,50/60Hz |

Features

- ✓ Fire rated to resistance of 90 Mins
- ✓ Swift connection - Loop in loop out wiring
- ✓ Effective acoustic installation and air leakage protection
- ✓ Available in Chrome, Satin Nickle & White Color
- ✓ High quality constructed durable steel body
- ✓ IP65 Protected for Outdoor use - IP 20 Protected for Indoor use
- ✓ Spring Clips for safer installation and easy Maintenance

Packaging

Unit Details

| | |
|----------------------|----------|
| Gross Weight(GW) Kgs | 0.2316 |
| Unit CBM | 0.000898 |

Listing Details

| | |
|----------------|---------------|
| EAN Code | 3800157626866 |
| Commodity Code | 9405109890 |

Master Box Packaging

| | |
|---------------------------------|----|
| Master Box Qty (Pcs Per Carton) | 50 |
|---------------------------------|----|

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES