



VT-701 GU10 FIXED FIRE RATED DOWNLIGHT FITTING IP20-CHROME

Dimensions
115x80mm


SKU:3682

3 YEARS
WARRANTY



Technical Information

Holder Type: GU10	IP Rating: IP20
Shape: Round	Dimmable: No
Cutting Size: 65mm	Warranty (Years): 3
Unit Color: CHROME	Operation Temperature: -25 to +50°C
Body Type: STEEL	Input Power: AC:220-240V,50/60Hz



Features

- ✓ Fire rated to resistance of 90 Mins
- ✓ Swift connection - Loop in loop out wiring
- ✓ Effective acoustic installation and air leakage protection
- ✓ Available in Chrome, Satin Nickle & White Color
- ✓ High quality constructed durable steel body
- ✓ IP65 Protected for Outdoor use - IP 20 Protected for Indoor use
- ✓ Spring Clips for safer installation and easy Maintenance

Packaging

Unit Details

Gross Weight(GW) Kgs	0.2316
Unit CBM	0.000898

Listing Details

EAN Code	3800157626873
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
---------------------------------	----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES