



15W

VT-16 15W FULL ROUND DOME LIGHT (MICROWAVE SENSOR) WITH SAMSUNG CHIP COLORCODE:4000K

Lumens 1400	Beam Angle 120	Dimensions Ø320x100mm
-----------------------	--------------------------	---------------------------------

Day White
SKU:804

3 YEARS
WARRANTY



Technical Information

Watts:	15	Sensor Type:	Microwave
Lumens:	1400	Long life:	30,000 Hours
Shape:	Round	LED Chip Type:	SMD-Samsung Chip
Beam Angle:	120	IP Rating:	IP65
Hold Time:	30s,40s,50s customized	Dimmable:	No
Detection Distance:	3-6M	Warranty (Years):	3
Detection Angle:	120/360	CRI:	>80
Detection Range:	Max 10Mx6M	Operation Temperature:	-20°C to +45°C
Unit Color:	White	Input Power:	AC:200-240V,50/60Hz
Body Type:	PC	Sensor Compatibility:	Yes

Features

- ✓ Premium quality LEDs with reliable lifetime
- ✓ Efficient thermal management technology
- ✓ 100% PC for Endurance/Durability
- ✓ Maintained operation suitable for long working hours
- ✓ High Power LED Samsung Chip
- ✓ Range of Dome Lights for Elegance-Ambience-Utility-Security-Weatherproof
- ✓ Constant current LED Driver for Instant start and consistent operation
- ✓ Complies with LM-80
- ✓ Applications - Office, Art Gallery, Display Case, Accent Lighting etc.

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.25
Unit CBM	0.011979

Listing Details

EAN Code	3800157636490
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	120

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES