



9W

VT-2189 9W A60 LED PLASTIC BULB COLORCODE:2700K B22

Equivalent 60W	Lumens 806	Beam Angle 200	Dimensions 60x106mm
--------------------------	----------------------	--------------------------	-------------------------------

Warm White
SKU:7422




2 YEARS
WARRANTY



Technical Information

EQ-WATTS: 60	Long life: 20,000 Hours
Watts: 9	LED Chip Type: SMD
Lumens: 806	IP Rating: IP20
Holder Type: B22	Dimmable: No
Shape: A60	Warranty (Years): 2
Beam Angle: 200	PF: >0.5
Unit Color: White	CRI: >80
Body Type: Thermoplastic	Operation Temperature: -20 to +45°C
Energy Rating: A+	Input Power: AC:220-240V,50Hz



Features

- ✓ Stable SMD technology which makes the product more reliable and durable
- ✓ Uses 80% less energy and lasts 20 times longer than Standard Bulbs
- ✓ LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- ✓ High endurance and Durability
- ✓ Excellent Heat Radiation Efficiency
- ✓ Aluminium & Thermoplastic Body options available
- ✓ High luminous efficacy & Low Power consumption
- ✓ Excellent Power factor & Integrated IC driver
- ✓ No Flickering - No UV Radiation - No Mercury
- ✓ Broad Range of holders like E27, E14, B22, B15 .
- ✓ Application - Residential Lighting, Commercial Lighting, Decorative, Living Room, Lounge etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs 0.0573

Unit CBM 0.000504

Listing Details

EAN Code 3800157634175

Commodity Code 9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton) 100

Qty Per Pallet 2500

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES