

## RGB Plug & Play Colour Changing LED Strip Kit - 5M RGB Strip 30LEDs/M, IR controller, UK Wall mounted driver

Partcode: ILSTRGBA081B / Page: 1



Effortlessly transform your room with Integral LED's Plug and Play Colour Changing Strip Kit. This convenient package comes with 5 metres of strip, a driver and a remote control. The ideal decorative lighting retail product.

### Product Details

Partcode: ILSTRGBA081B

Check Code: 582543

Range Name: Plug and Play Strip

Placement / Application: Decorative indoor

Market Segment: Commercial indoor, Residential indoor

Product Type: Colour strip

Warranty: 2 Years

CE / RoHS: Yes

### Physical Data

Base Colour: Matt white

*Partcode: ILSTRGBA081B / Page: 2*

**Physical Data**

Length: 5m

Width: 10mm

Weight (Unpackaged Single Unit): 390g

Strip Cut Points: 100mm

**Electrical Data**

Power Consumption: 7.2 Watts

Dimming: Dimmable with compatible dimming controller

LVD Certified: Yes

EN: IEC 62031, IEC 60598-1

**Light Data**

LEDs per meter: 30/m

Beam Angle: 120°

Colour Temperature: RGB

LED Type: Surface mounted device (SMD)

LED Size: 5050

Lifetime: 15,000 hrs

Partcode: ILSTRGBA081B / Page: 3

### Environmental

Lowest Operating Temperature: -25 degrees

Maximum Operating Temperature: 50 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788235293

Packaged Weight (Unit of 1): 405g

Length (unit of 1): 220mm

Width (unit of 1): 73mm

Depth (unit of 1): 280mm

**Outer packaging info available on website**

*Product data last updated on: Thursday, October 25, 2018 - 16:29*