

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5023820470

Status:

Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

1.25mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Single Row, Vertical, Tin Plating, 4 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-502382-001-001 (PDF)

Application Specification AS-502380-002-001 (PDF)

Packaging Specification SPK-502382-001-001 (PDF)


RoHS Certificate of Compliance (PDF)

Agency Certification		
UL		E29179
General		
Product Family		PCB Receptacles
Series		502382
Application		Signal, Wire-to-Board
Overview		CLIK-Mate Wire-to-Board Connectors
Product Name		CLIK-Mate
UPC		822350895217

Physical		
Circuits (Loaded)		4
Circuits (maximum)		4
Color - Resin		Natural
Durability (mating cycles max)		30
Glow-Wire Capable		No
Guide to Mating Part		Yes
Keying to Mating Part		Yes
Lock to Mating Part		Yes
Mated Height		7.80mm
Material - Metal		Copper Alloy
Material - Plating Mating		Tin
Material - Plating Termination		Tin
Material - Resin		High Temperature Thermoplastic
Net Weight		241.201/mg
Number of Rows		1
Orientation		Vertical
PCB Locator		No
PCB Retention		Yes
Packaging Type		Embossed Tape on Reel
Pitch - Mating Interface		1.25mm
Pitch - Termination Interface		1.25mm
Plating min - Mating		1.016µm
Plating min - Termination		1.016µm
Polarized to Mating Part		Yes
Polarized to PCB		No
Stackable		No
Temperature Range - Operating		-40° to +105°C
Termination Interface: Style		Surface Mount

Electrical		
Current - Maximum per Contact		1.0A
Voltage - Maximum		50V AC (RMS)/DC

Material Info



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

502382 Series

Mates With

502380 CLIK-Mate Housing

Reference - Drawing Numbers

Application Specification	AS-502380-002-001
Packaging Specification	SPK-502382-001-001
Product Specification	PS-502382-001-001
Sales Drawing	SD-502382-001, SD-502382-003

This document was generated on 10/18/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION