

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0797580008**  
**Status:** **Active**  
**Overview:** Pre-Crimped Leads  
**Description:** Pre-Crimped Lead Pico-SPOX Female-to-Pico-SPOX Female, 150mm, 24 AWG

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<u>79758</u>
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Pico-SPOX Crimp Terminals
Overview	<u>Pre-Crimped Leads</u>
Product Name	Pico-SPOX
UPC	884982052710

**Physical**

Cable Length	0.15m
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.494/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	24
Wire/Cable Type	UL 1061

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-797580001
---------------	--------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

79758 Series

**Use With**

Pico-SPOX Housings 87439