

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009931000

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK 3.96mm Crimp Terminal Housing, Friction Ramp, 10 Circuits, Glow-Wire Capable

Documents:

3D Model

Packaging Specification PK-3069-001-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-99020-0087-001 (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Comments

Crimp Housings

3069

Power, Wire-to-Board

This Molex product is manufactured from material that has the following ratings, tested by independent agencies :. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety; section 30 Resistance to heat and fire.<P><P>The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s).<P>If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.

KK® Interconnect System - Molex

KK 396

883906174255

Overview

Product Name

UPC

Physical

Circuits (maximum)

Circuits Detail

Color - Resin

Flammability

Gender

Glow-Wire Capable

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Temperature Range - Operating

10

10

Black

94V-2

Receptacle

Yes

Yes

Nylon

2.520/g

1

Bag

No

3.96mm

See Product Specification

Material Info

Engineering Number

3069-G10



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/61/2018 (27 June

2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

3069 Series

Mates With

2220 , 3190 , 3192 , 3243 , 3246 , 41661 , 41662 , 41671 , 41672 , 41681 , 41682 , 41701 , 41711 , 41721 , 41741 , 41761 , 41771 , 41772 , 41791 , 41792 , 42441 , 42461 , 42471 , 42491

Use With

2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG

Reference - Drawing Numbers

Packaging Specification	PK-3069-001-001
Product Specification	PS-99020-0087-001
Sales Drawing	SD-3069-GN***

This document was generated on 10/04/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION