

## GRIPPING PLIERS

No.	Description	Length mm	Headwidth mm	Finish	Weight g
3-631-15	Round nose pliers	120	10	plain jaws	55
3-632-15	Flat nose pliers	120	9	plain jaws	60
3-633-15	Snipe nose pliers	120	10	plain jaws	60
3-634-15	Snipe nose pliers, 120 angular	120	10	plain jaws	60



3-631-15



3-632-15



3-633-15



3-634-15



### 3-650 V

5-pcs. set consisting of:

#### 5 pliers from the CLASSICline series

lined up on the ESD tool holder „VARIO“  
for mounting or hanging

**Content:** Side cutters Art. No. 3-601-15, Round nose pliers Art. No. 3-631-15, Flat nose pliers Art. No. 3-632-15, Snipe nose pliers Art. No. 3-633-15 and Snipe nose pliers, angular Art. No. 3-634-15

**Weight:** 750 g



3-650 V

NEW



### 3-960 VC

6-pcs. set consisting of:

#### 4 pliers from the CLASSICline series 2 ESD Tweezers

lined up on the ESD tool holder „VARIO“  
for mounting or hanging

**Content:** Side cutters Art. No. 3-601-15, End cutters Art. No. 3-606-15, Flat nose pliers Art. No. 3-632-15, Snipe nose pliers Art. No. 3-633-15, 2 ESD Tweezers, angled Art. No. 5-055-13 and straight Art. No. 5-078-13



3-960 VC

NEW



### 3-960 C

ESD pliers set from the CLASSICline series

ESD pliers in a dissipative bag with slip-in compartments, 4-pcs., with dissipative, bicoloured hand guard

**Content:** Side cutters Art. No. 3-601-15, End cutters Art. No. 3-606-15, flat nose pliers Art. No. 3-632-15, Snipe nose pliers Art. No. 3-633-15



3-960 C