

2280 AND 2285 ESD PROFI SET TRENDY

23 pcs. ESD tool set
consisting of:

DESCRIPTION

Selected ESD tools in a handy plastic case made of dissipative material. The tools are clearly arranged in accurate-sized cutouts in dissipative hard foam. For individual needs, there are also 1 or 2 empty compartments.



No.	Description of individual tools	No.	Description of individual tools
2-620	PLCC extractor for easy removal of plug-in PLCC's	4-622	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 00, blade length 40 mm
3-133-13	Side cutter, Swedish design, 145 mm, for soft wire up to 4.0 mm Ø, for hard wire up to 2.5 mm Ø, lap joint, bright polished, chrome plated, with dissipative black hand guard	4-623	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 0, blade length 40 mm
3-651-15	Mini side cutters EUROline 120mm, with slim, rounded head, flush, for soft wire up to 1.5 mm Ø, medium hard wire up to 0.8 mm Ø, box joint, double leaf spring, fine polished and bright burnished, bicoloured hand guard, dissipative	5-049-13	SMD tweezers, 110 mm, straight, very sharply pointed, with ESD coating
3-682-15	Flat nose pliers EUROline, 130 mm, short, smooth jaws, finish as above	5-055-13	SMD tweezers, 120 mm, sickle-shaped, as above
3-683-15	Snipe nose pliers EUROline, 130 mm, short, smooth jaws, finish as above	5-059-13	SMD tweezers, 120 mm, flat, rounded tips, 2 mm width, as above
4-603	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 1.5 mm	6-661	TORX-screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size T 5, blade length 40 mm
4-605	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 2.0 mm	6-662	TORX-screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size T 6, blade length 40 mm
4-606	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 2.5 mm	6-663 L	TORX-screwdriver with dissipative handle, hardened over its full length chrome-plated, size T 7 with bore-hole, blade length 50 mm
4-621	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 000, blade length 40 mm	7-422	ESD brush with dissipative handle and bristles, 20 mm wide
		9-354	5 pcs. ESD-handling set (only in Set 2280), consisting of: foldable workbench pad (No. 9-354-10), 500 x 400 x 0.5 mm, black, dissipative, with 2 press-studs, adjustable and elastic contact bracelet (No. 9-342-1) with press-stud, highly elastic spiral cable (No. 9-342-2) with two press-studs, 2400 mm, earth wire with 2 press-studs, 1500 mm, insulated crocodile clip with banana plug and press-stud (No. 9-343).

NEW

2282 AND 2286 ESD PROFI SET TRENDY C

No.	Description of individual tools	No.	Description of individual tools
2-620	PLCC extractor for easy removal of plug-in PLCC's	4-623	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 0, blade length 40 mm
3-133-13	Side cutter, Swedish design, 145 mm, for soft wire up to 4.0 mm Ø, for hard wire up to 2.5 mm Ø, lap joint, bright polished, chrome plated, with dissipative black hand guard	5-049-13	SMD tweezers, 110 mm, straight, very sharply pointed, with ESD coating
3-602-15	Side cutters CLASSICline 115mm, with slim, rounded head, flush, bicoloured hand guard, dissipative	5-055-13	SMD tweezers, 120 mm, sickle-shaped, as above
3-632-15	Flat nose pliers CLASSICline as before, 120 mm, with short and plain jaws, dissipative, bicoloured hand guard	5-059-13	SMD tweezers, 120 mm, flat, rounded tips, 2 mm width, as above
3-633-15	Snipe nose pliers CLASSICline as before, 120 mm, with short and plain jaws	6-661	TORX-screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size T 5, blade length 40 mm
4-603	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 1.5 mm	6-662	TORX-screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size T 6, blade length 40 mm
4-605	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 2.0 mm	6-663 L	TORX-screwdriver with dissipative handle, hardened over its full length chrome-plated, size T 7 with bore-hole, blade length 50 mm
4-606	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 2.5 mm	7-422	ESD brush with dissipative handle and bristles, 20 mm wide
4-621	Cross-recess screwdriver as before, size PH 000, blade length 40 mm	9-354	5 pcs. ESD-handling set (only in Set 2280), consisting of: foldable workbench pad (No. 9-354-10), 500 x 400 x 0.5 mm, black, dissipative, with 2 press-studs, adjustable and elastic contact bracelet (No. 9-342-1) with press-stud, highly elastic spiral cable (No. 9-342-2) with two press-studs, 2400 mm, earth wire with 2 press-studs, 1500 mm, insulated crocodile clip with banana plug and press-stud (No. 9-343).
4-622	Cross-recess screwdriver as before, size PH 00, blade length 40 mm		



Outside dimensions (closed):
350 x 310 x 65 mm



2280: 1650 g
2285: 1500 g



2282: 23 Tools
2286: 18 Tools



2280 TRENDY ESD tool set with ESD handling Set
2285 TRENDY ESD tool set without ESD handling Set



Outside dimensions (closed):
350 x 310 x 65 mm



2282: 1650 g
2286: 1500 g



2282: 23 Tools
2286: 18 Tools



2282 TRENDY ESD tool set with ESD handling Set
2286 TRENDY ESD tool set without ESD handling Set

