

## 2250, 2252 AND 2270 ESD TOOL-SETS CARAT AND ACCENT



Special ESD service sets for maintenance and repair of mobile phones and other high-sensitivity electronic components. The ESD tools are clearly arranged in handy zipper-cases made of black, dissipative artificial leather.

### 2250 9 pcs. ESD tool-set CARAT consisting of:

No.	Description of individual tools	No.	Description of individual tools
3-672-15	End cutters EUROline, 130 mm, flush, for soft wire up to 0.8 mm Ø, medium hard wire up to 0.6 mm Ø, cutting edge 20° angular, finish as above	4-621	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 000, blade length 40 mm
3-683-15	Snipe nose pliers EUROline, 130 mm, short, smooth jaws, finish as above	4-623	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 0, blade length 40 mm
4-603	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 1.5 mm	5-191	Tweezers made of dissipative, black, glass fiber-reinforced plastic material, 120 mm, straight, rounded tips, 2 mm wide
4-605	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 2.0 mm	6-661	TORX-screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size T 5, blade length 40 mm
		6-663 L	TORX-screwdriver with dissipative handle, hardened over its full length chrome-plated, size T 7 with bore-hole, blade length 50 mm

NEW

### 2252 9 pcs. ESD tool set CARAT C consisting of:

No.	Description of individual tools	No.	Description of individual tools
3-606-15	End cutters CLASSICline, 120 mm, with slim, pointed head, special flat cutting edge, cutting shape flush, dissipative, bicoloured hand guard	4-623	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 0, blade length 40 mm
3-633-15	Snipe nose pliers CLASSICline as before, 120 mm, with short and plain jaws	5-191	Tweezers made of dissipative, black, glass fiber-reinforced plastic material, 120 mm, straight, rounded tips, 2 mm wide
4-603	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 1.5 mm	6-661	TORX-screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size T 5, blade length 40 mm
4-605	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 2.0 mm	6-663 L	TORX-screwdriver with dissipative handle, hardened over its full length chrome-plated, size T 7 with bore-hole, blade length 50 mm
4-621	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 000, blade length 40 mm		

### 2270 9 pcs. ESD tool set ACCENT consisting of:

No.	Description of individual tools	No.	Description of individual tools
3-601-15	Side cutters CLASSICline 115mm, with slim, rounded head, semi flush, bicoloured hand guard, dissipative	4-621	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 000, blade length 40 mm
3-633-15	Snipe nose pliers CLASSICline as before, 120 mm, with short and plain jaws	4-623	Cross-recess screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size PH 0, blade length 40 mm
4-603	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 1.5 mm	5-191	Tweezers made of dissipative, black, glass fiber-reinforced plastic material, 120 mm, straight, rounded tips, 2 mm wide
4-605	Slotted screwdriver with dissipative handle and centering head, hardened over its full length, matt chrome-plated, 40 x 2.0 mm	6-661	TORX-screwdriver with dissipative handle, hardened over its full length, matt chrome-plated, size T 5, blade length 40 mm
		6-663 L	TORX-screwdriver with dissipative handle, hardened over its full length chrome-plated, size T 7 with bore-hole, blade length 50 mm



Outside dimensions (closed):  
190 x 135 x 35 mm



360 g



9 Tools



**2250 CARAT** 9-pcs. ESD tool set



Outside dimensions (closed):  
190 x 135 x 35 mm



360 g



9 Tools



**2250 CARAT C** 9-pcs. ESD tool set



Outside dimensions (closed):  
190 x 135 x 35 mm



360 g



9 Tools



**2270 ACCENT** 9-pcs. ESD tool set

