Upgraded Chip Newly 3d printer

Simple but exquistie

Matrix automatic leveling

Great News For Users who have level troubles.

Imported Bill Touch automatic leveling device, 9-point leveling, simplifying the leveling process.

Porblems a lot?

STILL troubling you?

THE PROBLEM

SWEEP THE FLOOR TO

TROUBLE A LOT OF ARE THESE QUESTIONS BOTHERING YOU





EASILY SOLVED

Simple but exquistie

4+2 screws for quick installation

Two modules, just needs six screws and can be quickly installed





After





More intelligent 3D printer

More upgrade More Surprise

Stable and reliable, continuously print 200 hours without any problem.



Automatic leveling



Quickly heating up



Resume printing



High precision printing



Filament detection



Brand power supply

CR20 Pro Parameter

Molding Tech. FDM

Printing Size

220*220*250mm

Printing Speed

≤100mm/s, Normal 30-60mm/s

Precision

±0.1mm

Slice Thickness

Nozzle Diameter

Standard0.4mm,can be in 0.2,0.3mm

Nozzle Number

Nozzle Temp.

≤250°C

Bed Temp.

≤110°C

Working Mode

Online or SD card offline

File Format:

STL,Obj,amf

Slice Software

Cura/Repetier-Host/Simplify3D

Total Power

270W

Fliament


PLA, ABS, TPU


Fliament Diameter 1.75mm

Power Supply

Input:AC 100-120V/6.8A 200-240V/3.4A 50/60Hz


Output:DC 24V





Newly Cmagnetic sticker

Cmagnetic sticker, Better adhere to the platform, No need to use textured paper and glue anymore.easier to remove the model and solve the printing edge problem, more cost-effective.



High Standard Structure

Patent Technology 2: The V-profile pulley moves more stable and smoothly, with lower noise and wear resistance.






Imported Teflon tube

Imported blue Teflon tube with high temperature resistant makes the feeding smoother, but improves the printing quality.







Intelligent 3D printer

Resume printing While power-off


Safely protect the power supply, with this function, which can help achieving long-time printing.




PRODUCT DETAILS


All real shots















Brass nozzle

APPLICATION FIELD

All real shots



Industrial



Architectural



Medical area



Movie property



Home



3D portrait

More fields are waiting for you to discover.....

CARTON SIZE All real shots



Printer Size: 420*440*470mm Gross Weight: 10.1KG

Package Size: 495*485*295mm



UpgradedExtruder

Patent Technology 1: MK-10 Extrusion mechanism, reducing the risk of plugging and spillage.





Patent No.: 2016200045384

COMPANY



Always chase better, never fall behind

Creality 3d always committed to continuously improving the production of 3D printers with higher technology capabilities.



Brand Culture
Founded in 2014, Shenzhen Chuangxiang 3D Technology Co., Ltd. is an R&D n 3D printing industry in China, dedicated to building 3D Creakuty 3D will develop 3D printing and the Intern

tinuously innovate in technology, and continuously optimize product lines. Committed to creating a special 3D printing production kingdom, to meet your imagination of

ree-dimensional molding, so that your dreams are possible.

People enjoy the convenience brought by 3D printing technology.

Honor





