

TE08250

Telephone KX-TGF320E

General	Colour	M[Metallic Black]
	Cordless Handset (Quantity)	1
	Frequency	1.9 GHz
	Frequency Range	1.88 GHz - 1.90 GHz
	Number of Channels	120 Channels
	System	DECT
	DECT Security Mode	-
	GAP	Y
	Number of Phone Lines	1
	Multiple Cordless Handsets Capability	Up to 6 Handsets
	Multiple Base Units Capability	-
	LCD Language	Catalan, Danish, Dutch, English, Finnish, French, German, Greek, Italian, Norwegian, Portuguese Spanish, Swedish, Turkish
	Wi-Fi® Connection	-
	Mobile Connection	-
	Bluetooth® Class	-

	Android™ OS Version	-
Power Saving	Low Radio Power	Y
	One Touch Eco Mode	Y
Smartphone Connect		-
Multiple Smartphones Capability		-
Supported Devices		-
Wireless Network Standard		-
Simplified Configuration		-
Easy Wi-Fi Setup Button		-
Wi-Fi Repeater Mode		-
Phonebook Copy from Smartphone		-
Ringtone Copy from Smartphone		-
Wallpaper Image Copy from Smartphone		-
Conference Call with Outside Landline and Smartphone		-
Transferring Landline Call (between Smartphone and Handsets)		-
Playing Aanswering System Messages		-
Convenience	Key Finder Compatible	Y
	Multiple Key Finder Capability	Up to 4 Key Finders

	<b>Repeater Available</b>	Y
	<b>Clear Sound</b>	Y
	<b>Noise Reduction (Cordless Handset)</b>	Y
	<b>Noise Reduction (Answering System)</b>	Y/* When using the base unit or handset to listen to messages, the noise reduction feature is activated automatically.
	<b>Customized Sound System (Equalizer)</b>	Treble/Alto/Bass
	<b>Compatible with Hearing Aid T-Coil (TIA-1083 Compliant)</b>	-
	<b>Power Back-Up Operation</b>	Y/* The base unit gets temporary power supply from 2 AAA batteries in the case of a power outage.
	<b>Baby Monitor</b>	Y/* Optional handset is required for the internal baby monitor feature.
	<b>Smart Function Key</b>	-
	<b>Any Key Answer</b>	Y
	<b>Do Not Disturb Mode</b>	Y
	<b>Bypassing Do Not Disturb Mode (Specified Phonebook Category)</b>	Y/* Requires subscription to Caller ID service offered by your provider/telephone company.
	<b>SMS</b>	-
	<b>Call Restriction</b>	Y
	<b>Distress Call</b>	-
	<b>Conference Call with Outside Line</b>	Y/3Way/* 3Way: Base unit - Handset - Landline, Handset - Handset - Landline/** Optional handset is required in case of "Handset - Handset - Landline".

	<b>Call Share</b>	Y
	<b>Intercom (Cordless Handset to Base Unit)</b>	Y
	<b>Intercom (Cordless Handset to Cordless Handset)</b>	Y/* Optional handset is required.
	<b>Intercom All</b>	Y (To Base Unit and All Handsets)/* Optional handset is required.
	<b>Clock</b>	Y
	<b>Calendar/Scheduler</b>	-
	<b>Alarm (Wake-up / Memo alarm)</b>	Y/Y
	<b>Advanced Alarm (A day of the week / Snooze)</b>	Y/Y
	<b>Bluetooth Headset Capability (HSP Support)</b>	-
	<b>Bluetooth Audio Headphone/Speaker Capability (A2DP Support)</b>	-
	<b>Google Play™ Support</b>	-
<b>Caller ID/ Phonebook</b>	<b>Caller ID</b>	Y/* Requires subscription to Caller ID service offered by your provider/telephone company.
	<b>Caller ID Memory</b>	50 items/* Requires subscription to Caller ID service offered by your provider/telephone company.
	<b>Call Waiting Caller ID</b>	Y/* Requires subscription to both Caller ID and Call Waiting with Caller ID services offered by your provider/telephone company.
	<b>Category Display Colours</b>	-
	<b>Talking Caller ID (Cordless Handset)</b>	Y/* Requires subscription to Caller ID service offered by your provider/telephone company./** Name

		pronunciation may vary.
	<b>Talking Caller ID (Base Unit)</b>	Y/* Requires subscription to Caller ID service offered by your provider/telephone company./* Name pronunciation may vary.
	<b>Talking Caller ID Language</b>	English/* Requires subscription to Caller ID service offered by your provider/telephone company./* Name pronunciation may vary.
	<b>Nuisance Call Block</b>	Y(100 numbers)/* Requires subscription to Caller ID service offered by your provider/telephone company./** Requires number registration in the nuisance call block list.
	<b>Block Range of Numbers</b>	Y/* Requires subscription to Caller ID service offered by your provider/telephone company.
	<b>Block Numberless Call</b>	Y/* Requires subscription to Caller ID service offered by your provider/telephone company./** Numberless calls cannot be blocked depending on the service of your provider/telephone company.
	<b>Handset Phonebook Memory (Name/Number)</b>	-
	<b>Base Unit Phonebook Memory (Name/Number)</b>	100items/(16char/24digits)
	<b>Shared Phonebook</b>	Y
	<b>Phonebook Copy from Mobile Phone via Bluetooth</b>	-
	<b>Chain Dial (Cordless Handset)</b>	Y
	<b>Chain Dial (Base Unit)</b>	Y
<b>Cordless Handset</b>	<b>LCD</b>	1.8 inch (4.6 cm)/Full Dot Monochrome/103 x 65 pixels
	<b>LCD Backlight Colour</b>	White
	<b>Touchscreen</b>	-

	Front Camera	-
	Rear Camera	-
	LED Flash	-
	GPS	-
	SD Memory Card Slot	-
	USB Jack	-
	USB Version	-
	Illuminated Keypad	Amber
	Speakerphone (Volume Steps)	Y(7-step)
	Full Duplex Speakerphone	Y
	Icon Operation (Number of Icons)	Y(6)
	Ringer Pattern (Tone+Melody)	40
	Polyphonic Ringer Melody	32 chord
	Ringer Volume Steps	6+OFF
	Receiver Volume Steps	5
	Redial Memory	10(Name & Number)/* Requires registration in the phonebook to display the name.
	Digits of Redial Number	24
	Auto Redial	-

	<b>Ringer Indicator (Colour)</b>	-
	<b>Hold</b>	Y
	<b>Mute</b>	Y
	<b>Key Lock</b>	Y
	<b>Headset Jack</b>	Y
	<b>Secure Grip</b>	-
	<b>Short Stroke Key</b>	-
	<b>Wall Mountable (Charger)</b>	-
<b>Base Unit</b>	<b>Dial Keypad</b>	Y
	<b>Corded Handset</b>	Y
	<b>Display</b>	3.4inch (8.6 cm)/Monochrome/103 x 65pixels/3Line+Softkey or 2Line+Pict+Softkey
	<b>Speakerphone (Volume Steps)</b>	Y (1-8)
	<b>Ringer Pattern (Tone+Melody)</b>	1(1+0)
	<b>Ringer Volume Steps</b>	6+OFF
	<b>Redial Memory</b>	10(Name & Number)/* Requires registration in the phonebook to display the name.
	<b>Auto Redial</b>	-
	<b>Mobile Locator</b>	-
	<b>Hold</b>	Y

	<b>Mute</b>	Y
	<b>Handset Locator</b>	Y
	<b>Wall Mountable</b>	Y
<b>Answering System</b>		Y
<b>Total Recording Time</b>		About 40 min
<b>Fast-Forwarding and Rewinding Message</b>		Y
<b>Audible Message Alert</b>		Y(Base Unit)
<b>New Message Notification by a Call</b>		Y
<b>Announcement Language of New Message Notification</b>		English
<b>New Message Notification by an SMS</b>		-
<b>Visual Message List (Handset LCD)</b>		-
<b>Recording Conversation</b>		-
<b>Speaker Volume Steps(Base Unit Speaker)</b>		8
<b>Call Screening (Cordless Handset)</b>		Y
<b>Call Screening (Base Unit)</b>		Y
<b>Language of Pre-recorded Greeting Message</b>		English
<b>Remote Operation from Outside (DTMF)</b>		Y
<b>Toll Saver (New Messages Recorded / No New Message)</b>		2/5



Accessories	Key Finder Included (Quantity)	-
	Repeater Included	-
	Belt Clip Included	Y
Optional Handset		KX-TGFA30
Others	Radiation Free (Eco Mode Plus)	Y
	Rechargeable Battery	Ni-MH(AAA x 2)
	Talk Time	Up to 17hours
	Standby Time	Up to 330hours
	Charge Time	About 7 hours
Power Consumption	Base Unit Standby Power Consumption	0.6W
	Charger Standby Power Consumption	0.12W
Dimensions/ Weight	Key Finder Dimensions (W x D x H)	-
	Repeater Dimensions (W x D x H)	-
	Charger Weight	Approx. 40 g
	Interface Box Weight	-
	Key Finder Weight	-
	Repeater Weight	-