

DYMO 12mm LetraTAG Plastic tape label-making tape



- » Brand: DYMO
- » Product name: 12mm LetraTAG Plastic tape
- » Product code: S0721660
- » EAN/UPC code: 5411313912211

Marketing text

Specs

Marketing text

These tapes are designed for your convenience for either LetraTag model. Use them to organize your basement, garage, kitchen or office in a variety of styles that adhere to a range of surfaces, in a rainbow of eye-catching colors.

These 12mm non-glossy tapes are easy to peel and cut, with quick-change cassettes for "on-the-fly" labelling. Think of LetraTAG paper tape as the economical solution for labelling almost anything, anywhere in your home.

Compatible with all LetraTag label makers.

Specs

Features

<u>Material</u>	Polyester
Customs code	8473408000
<u>Country of origin</u>	Belgium

Packaging content

Package type Blister

Weight & dimensions

Tape length 4 m
Quantity per pack 1 pc(s)
Package width 22 mm
Package depth 96 mm
Package height 146 mm
Package weight 28 (tbc)

Inner carton

Quantity inner carton 10 pc(s)
Width inner carton 10.8 cm
Depth inner carton 13.7 cm
Height inner carton 16.1 cm

Inner carton

Net weight inner carton 0.280 kg
Gross weight inner carton 0.329 kg

Outer carton

Quantity outer carton 50 pc(s)
Width outer carton 16.5 cm
Depth outer carton 53.5 cm
Height outer carton 15 cm
Net weight of outer carton 1.400 kg
Gross weight of outer carton 1.625 kg
Volume outer carton 13.2413 L

Other features

Tape size 1.2 cm
Package volume 0.3084 L