

No.	Length		Finish / Model	Weight g
	mm	inch		
5-066	120	4 3/4"	30° angled, 2.5 mm width 8b SA	15
5-066-13	120	4 3/4"	as before, with ESD coating	15
5-067	120	4 3/4"	tip 45° angled, 2 mm width 12 SA	15
5-067-13	120	4 3/4"	as before, with ESD coating	15
5-068	120	4 3/4"	tip angled, 1.6 mm width, 13 SA	13
5-068-13	120	4 3/4"	as before, with ESD coating	13
5-071	85	3 3/8"	thin, straight-pointed, OC SA	8
5-071-13	85	3 3/8"	as before, with ESD coating	8
5-072	110	4 3/8"	schmal, straight-spitz, 3c SA	11
5-072-13	110	4 3/8"	as before, with ESD coating	11
5-073	140	5 1/2"	long-thin, straight, very sharply pointed, SS SA	13
5-073-13	140	5 1/2"	as before, with ESD coating	13
5-074	120	4 3/4"	straight, pointed, 1 SA	14
5-074-13	120	4 3/4"	as before, with ESD coating	14
5-075	140	5 3/4"	straight, very sharply pointed, grip surface offset, 60 SA	13
5-075-13	140	5 3/4"	as before, with ESD coating	13
5-076	120	4 3/4"	rigid, straight, pointed, 00 SA	19
5-076-13	120	4 3/4"	as before, with ESD coating	19
5-077	130	5 1/8"	wide, tapering, pointed, AA SA	16
5-077-13	130	5 1/8"	as before, with ESD coating	16
5-078	130	5 1/8"	tapering, chisel, 1 mm width, PSF SA	16
5-078-13	130	5 1/8"	as before, with ESD coating	16
5-083	140	5 3/4"	straight, pointed	8
5-083-13	140	5 3/4"	as before, with ESD coating	8



TWEEZERS

NEW

## CUTTING TWEEZERS

Made from Carbon Steel, extremely hard, excellent sharpness at the cutting edges. For cutting of soft copper, gold and silver wires up to 0.25 mm Ø.

5-079	115	4 1/2"	Carbon Steel, matt finish 15 AGW	25
5-079-13	115	4 1/2"	as before, with ESD coating	25

