

- a good companion for rough cleaning and DIY projects

The Multi II is a good companion to the Do it yourself person in any house. It is also a good second vacuum cleaner dedicated to dirt and debris inside as well as outside the house, car or the like.

The Multi II - the second generation of Multipurpose vacuum cleaners - offer a filter cleaning indicator on all models. This is a warning telling you that the vacuum is loosing performance and it is about time to clean or replace the filter.

The Multi II also offers a Push&Clean function to clean the filter. This function is a semi-automatic method of cleaning the filter by creating an airwave hitting the filter from inside out.

The combination of filter cleaning indicator and Push&Clean function makes this machine a truly unique offer. Together these features ensures a consistent high cleaning performance.

- Filter clean indicator for continued high performance
- Push&Clean, a semi-automatic filter cleaning function
- Sturdy build with a robust 1200 W engine for long life
- High suction power for efficient cleaning
- Blow function provides another cleaning option
- 22 l container with good net filling capacity
- Polypropylene container for easy cleaning
- Soft start by attached power tool



Picture shown may not represent model quoted

● Standard equipment

Included accessories		Ref. no.	Min. required	NILFISK MULTI II 22 T INOX EU	MULTI II 22T UK
Nozzle - Vacuum					
	FLOOR NOZZLE D36 W/D 1 PCS	107417197	0	•	•
Dust Bag and Filter					
	FILTER KIT 1 PCS	107417194	0	•	•

Model	NILFISK MULTI II 22 T INOX EU	MULTI II 22T UK
Ref. no.	18451577	18451585

PRODUCT FEATURES

Dust bag 1 pcs.	•	•
Tube holder	•	•
Compact design		
Softstart	•	•
Tool tray	•	•
Filter bag	•	•
Wet & dry performance	•	•



- a good companion for rough cleaning and DIY projects

Model	NILFISK MULTI II 22 T INOX EU	MULTI II 22T UK
Ref. no.	18451577	18451585

#### PRODUCT FEATURES











Push&Clean filter cleaning	•	•
Suction control on hand tube	•	•
Automatic on/off - electric tools	•	•
Storage of accessories	•	•
Cable storage	•	•
Variable speed control		
Blow function	•	•
Steel container	•	
Quick park	•	•
Hose holder	•	•
Container lift/tilt handle		•
Filter Clean Indicator	•	•
Parking function	•	•
French version		
Large wheel - 2 pcs.	•	•

Technical specifications	NILFISK MULTI II 22 T INOX EU	MULTI II 22T UK
Max. suction power (W)	270	270
Power Pmax (W)	1200	1200
Power Piec (W)	1130	1130
Mains connection (V~/Hz/A)	220-240/ 1~/ 50/60	220-240/ 1~/ 50/60
Vacuum (mbar/kPa)	200 / 20	200 / 20
Sound level lpa/lwa (dB(A))	85/ 72	85/ 72
Cable length (m)	5	5
Container volume (l-max)	22	22
Vacuum tube diameter (mm)	36	36
Hose length (m)	2.2	2.2
Plug for electric tools (W)	Yes, 1100W	Yes, 1100W
Length x width x height (cm)	42.6 x 37.4 x 59.9	42.6 x 37.4 x 59.9
Weight (kg)	9.20	7.85












- a good companion for rough cleaning and DIY projects

● Standard equipment, ○ Supplementary accessories, □ Mountable equipment

Accessories		Ref. no.	Min. required	NILFISK MULTI II 22 T INOX EU	MULTI II 22T UK
<b>System 36 Tube</b>					
	EXTENSION TUBE D36 2X500MM ALU	107400032	0	○	○
	EXTENSION TUBE D36 2X515MM PLASTIC	40696	0	○	○
	TELESCOPIC TUBE Ø36X550-970 SS	47109	0	○	○
<b>System 36 Brush/Universal Nozzle</b>					
	SUCTION BRUSH D36 BLACK	302002509	0	○	○
	UNIVERSAL NOZZLE D36X115	14295	0	○	○
<b>System 36 Crevice/Cone Nozzle</b>					
	CREVICE NOZZLE D36X200	29541	0	○	○
<b>Tube</b>					
	TELESCOPIC TUBE PLAST.-KIT	107402705	0	○	○
<b>System 36 Vac Floor Nozzle</b>					
	COMBI NOZZLE Ø36X260MM	302002365	0	○	○
	FLOOR NOZZLE D36x300MM W/D KIT	107402706	0	○	○
	SUCTION NOZZLE WATER Ø36 300MM	63992	0	○	○



- a good companion for rough cleaning and DIY projects

Accessories		Ref. no.	Min. required	NILFISK MULTI II 22 T INOX EU	MULTI II 22T UK
<b>Accessory Kit</b>					
	BLOW NOZZLE KIT	107402483	0	○	○
	CONVENIENCE KIT-TOPBOX	107417191	0	○	○
	PREMIUM CAR KIT-TOPBOX	107417190	0	○	○
	WALL DRILL KIT	107402478	0	○	○
<b>Hose and Connection</b>					
	SUCTION HOSE 2.5M 1 PCS	107417192	0	○	○
	SUCTION HOSE 4M 1 PCS	107417193	0	○	○
<b>Dust Bag and Filter</b>					
	DUST BAG FLEECE 22L/30l 4 PCS	107417195	0	○	○
	FILTER KIT 1 PCS	107417194	0	●	●
<b>Nozzle - Vacuum</b>					
	FLOOR NOZZLE D36 W/D 1 PCS	107417197	0	●	●