


## P3158

### Pylon Probe

Product Family: Pylon



#### Mechanical:

**Test Center (mil):** 100

**Test Center (mm):** 2.54

**Overall Length (mil):** 970

**Overall Length (mm):** 24.64

**Full Travel (mil):** 170

**Full Travel (mm):** 4.32

**Recommended Travel (mil):** 114

**Recommended Travel (mm):** 2.90

#### Thermal:

**Max Operating Temp (°C):** 105

**Min Operating Temp (°C):** -55

#### Electrical:

**Current Rating (Amps):** 8

**Average DC Resistance lower than (mOhm):** 10

#### Materials & Finishes:

**Plunger Material:** Heat-treated BeCu or Steel, Gold plated over hard Nickel

**Barrel Material:** Phosphor Bronze, Gold plated

**Ball Material:** Stainless Steel

#### Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 2.70 (72.00) - 6.90 (196.00) - Music Wire

Alternate - 1.30 (37.00) - 2.80 (79.00) - Music Wire

#### Body Type

Straight

Pylon Bend

#### Additional information:

Use ARIT-25 tool for installation

TIPS:

Tip Materials: BeCu, Gold plated, Steel

Tips:



Related Products:

