


P2757 Replaceable Probe Product Family: Pylon



Springs

Force Type – Preload in oz (g) – Rec. Travel in oz (g) – Spring Material

 $\begin{array}{l} {\sf Standard - 2.00 \; (57.00) - 4.00 \; (113.00) - Stainless \; Steel} \\ {\sf Alternate - 3.50 \; (99.00) - 6.85 \; (194.00) - Stainless \; Steel} \\ \end{array}$

Body Type

Straight Pylon Bend

Mechanical:

Test Center (mil): 187
Test Center (mm): 4.75
Overall Length (mil): 1,210
Overall Length (mm): 30.73

Overall Length Remark: Tip 2C: 1140 mil (28.96 mm) Tip 1W: 1205 mil (30.61 mm) Tip 2W: 1205 mil (30.61

mm)

Full Travel (mil): 230 Full Travel (mm): 5.84

Recommended Travel (mil): 167
Recommended Travel (mm): 4.24

Thermal:

Max Operating Temp (°C): 150 Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 20

Average DC Resistance lower than (mOhm): 10

Materials & Finishes:

Plunger Material: Heat-treated BeCu, Gold plated over

hard Nickel

Barrel Material: Phosphor Bronze, Gold plated

Ball Material: Stainless Steel

TIPS:

Tip Materials: BeCu, Gold plated

Tips:

P2757-1C



P2757-1R



P2757-1V



P2757-1W



P2757-2W




P2757-3W




Related Products:

S2757-2ED



S2757-2ETD



S2757-2EWWD

