

SCREWDRIVER

Screwdriver extra short

Blade: chrome vanadium, nickel-plated with black tip
 Handle: impact-resistant, two-coloured plastic



No.	Size PH	Blade-length mm	Blade-Ø mm	Handle size mm	Weight g
4-261	01	25	4.5	55 x 30	30
4-262	02	25	6.0	55 x 30	35



4-261

No.	Blade-length mm	Blade-width mm	Blade-thickness mm	Handle size mm	Weight g
4-321	25	4.0	0.8	55 x 30	30
4-322	25	6.5	1.2	55 x 30	35



4-321

Miniature screwdriver

Blade: special steel nickel-plated
 Handle: black plastic



4-301	40	1.8	0.5	45 x 9	3
-------	----	-----	-----	--------	---



4-301

Screwdriver for headless screws

Blade: Chrome vanadium, nickel-plated
 Handle: impact resistant, black plastic



4-311	80	2.8	0.6	60 x 11	12
-------	----	-----	-----	---------	----



4-311

Installation screwdriver

Blade: special steel, nickel-plated
 Handle: impact resistant, bicoloured and multicomponent, with anti-slip protection and practical hanging up hole



4-331	65	6.0	1.0	100 x 21	40
-------	----	-----	-----	----------	----



4-331

VDE voltage tester 220 - 250 V. DIN VDE 0426 part 6:1977-04



Blade: chrome-vanadium, nickel-plated, completely insulated
 Handle: transparent plastic

4-343 VDE	60	3.0	0.7	76 x 15	15
4-344 VDE	110	3.5	0.7	92 x 18	31



4-343 VDE

Offset screwdriver

Material: chrome vanadium, nickel-plated, plastic handle



No.	Total-length mm	Blade-width mm	Blade-thickness mm	Blade-Ø mm	Weight g
4-351	100	4.0	0.65	4.5	12

4-820 60-piece miniature screwdriver stand

Content: 60 screwdrivers with tool steel blades, 40 x 1.8 mm and transparent yellow plastic handles
 Weight: 235 g



4-820