

128.835UK

Page 1 of 1

Brand name	AV:Link	Color	Black	Inner qty	
		Packed	Gift Box	Outer qty	20
Date added	26/01/2018	Barcode	5015972192153	Pallet qty	



4K HDMI Switch / Splitter 2x4

A 4K HDMI splitter to switch between 2 source devices, with up to 4 display outputs. Use with HDMI cables of a combined 25m per output for HD resolution, or a combined 16m per output for 4K resolution, without signal loss. SPDIF and 3.5mm jack outputs allow the audio signal of the selected source device to simultaneously be channelled through a separate sound system; ideal for hospitality and entertainment venues. Supplied with IR remote to switch between sources.

- Simple connection and operation
- Gold plated HDMI connectors for optimum signal transfer
- Supports HDMI v1.4b resolutions up to 3840 x 2160 @ 30Hz
- Supports DTS-HD, Dolby True, DTS, Dolby-AC3 and DSD audio formats
- Digital SPDIF and analogue 3.5mm jack audio outputs
- Ideal for entertainment, hospitality and other commercial venues with multiple displays
- IR remote and UK power adaptor supplied

HDMI version	v1.4b	Transmission distance	25m max HD or 16m max 4K (15m input/10m output @ 1080p and 8m input/output @ 4K)
Resolution	Up to 3840 x 2160 @ 30Hz	Max. working current	1000mA
Display colours	8/10/12bit deep colour	Operating temperature range	-15°C ~ +55°C
Audio format	DTS-HD, Dolby True, DTS, Dolby-AC3 and DSD	Dimensions	200 x 75 x 25mm
Max. bandwidth	300MHz	Weight	280g
Max. baud rate	3Gbps		

Stock Code	Model	Description	Colour	Packed
128.835UK	HSS24	HDMI Switch/Splitter 2x4	Black	Gift Box