

ARCA ARK1085CHFTSSM



Order symbol:	ARK1085CHFTSSM
Product nbr:	8561468
Description:	PC Enclosure
Remarks:	Hinged opaque flat cover w/S.S. Lockable twist latch, base includes 1/2 and 3/4 inch knock-outs and metal mouting feet.

EAN: 6418074096449
El. number:
Finland:

Sample photo

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:	
mm:	254	203	127	ALBP108	Aluminum Back Panel
inch:	10.0	8.0	5.0	ADFP108	Dead Front Panel w/ screws
Materials:				ASP108	Aluminum Swing Panel
				ASPK108	Swing Panel Kit incl. Panel
				ASPHK10	Swing Panel Kit w/o Panel
				AMFL8	8" Mounting Flange Set
Material:	Polycarbonate			Rating:	
Base colour:	RAL 7035 -light grey			Ingress Protection (EN 60529): IP66/IP67	
Cover screws material:	Stainless steel			Impact Resistance (EN 62262): IK09	
Cover colour:	RAL 7035 -light grey			Electrical insulation: Totally insulated	
Gasket material:	Polyurethane			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperatures:				UV resistance: UL 508	
				Flammability Rating: UL 508	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
Accessories:				Certificates:	
ABP108 Painted Steel Back Panel				Gost R	

