



Simply clamp this work light onto your ladder or lift, point the light wherever you need it and get to work. The head on this LED light rotates 360° and pivots 90° so that you can direct the light exactly where it is needed. When the light is on, the glow head self-charges so that you can locate it if it falls – and don't worry, because this durable light is rated for drops of up to 10'. The light can be clamped, stand on its own or is easily hand held, making the versatile, durable Klein Tools clamping work light a must for the job site.

Specifications

Type:	Clamping Work Light	Application:	Work Light
Special Features:	360° Rotating and 90° Pivoting Head	Overall Length:	11.2" (284.5 mm)
Overall Height:	2.8" (71.1 mm)	Overall Width:	2.5" (63.5 mm)
Diameter:	—	Material:	ABS, PC, Stainless Steel
Lumens:	High: 250, Low: 125	Bulb Type:	LED
Battery Life:	High: 8 hrs., Low: 10 hrs.	Batteries:	4 x AA
Temperature Range:	-20° to +120° F (-29° to +49° C)	Drop Protection:	10' (3 m)
Standard:	—	Included:	Batteries
Weight:	15.3 oz (434 g)		