



Crimps and seats UG, UR and UY connectors. Curved handles for greater control. Induction hardened side-cutting knives for long life. 11/16-Inch jaw width.

Specifications

Type:	Side cutting/Connector crimping	Application:	UG, UR and UY connectors
Overall Length:	5.813" (147.7 mm)	Jaw Length:	1.094" (27.8 mm)
Jaw Width:	0.688" (17.5 mm)	Jaw Thickness:	3/8" (9.5 mm)
Knife Length:	0.5" (12.7 mm)	Handle Colour:	Yellow
Handle Finish:	Plastic dipped	Handle Length:	3.375" (85.7 mm)
Insulated:	No	Tether capable:	No
Weight:	0.25 lb (0.11 kg)		