



Crimps and seats Scotchlok UG, UR and UY connectors. Hot-riveted joint for smooth action and no handle wobble. Curved handles for greater control. Induction hardened side-cutting knives for long life. Spring-loaded action for self-opening. Scotchlok is a registered trademark of 3M.

Specifications

Type:	Connector Crimping	Application:	Scotchlok UG, UR and UY connectors
Special Features:	Spring-loaded	Overall Length:	5.813" (147.7 mm)
Jaw Length:	1.094" (27.8 mm)	Jaw Width:	0.688" (17.5 mm)
Jaw Thickness:	3/8" (9.5 mm)	Jaw Capacity:	1.27" (32.3 mm)
Knife Length:	0.5" (12.7 mm)	Joint Type:	Hot-Riveted
Handle Colour:	Yellow	Handle Finish:	Plastic dipped
Handle Length:	3.375" (85.7 mm)	Insulated:	No
Tether capable:	No	Weight:	0.25 lb (0.11 kg)